

DATA SHEET

0164012

IEC compensating cable KN 20 L 2x1,5

valid from:

01.12.2008

Application

The compensating cable KN 20 L 2 x 1,5 mm² is a PVC insulated cable with aluminium foil screen which transmits the thermoelectric voltage of NiCr/Ni thermocouples. It is for flexible use and fixed installation in dry and damp rooms with medium mechanical load. They may only be installed outdoors with UV protection and in observation of the max. permitted temperature range. The overlapping foil wrapping screens the cores against electromagnetical interference.

Design

Conductor 1,5 mm² (48 x 0,20 mm)

Conductor material KCA alloying, accuracy class 2 according IEC 60584

Positive conductor: Fe (iron)

Negative conductor: CuNi (cupronickel)

Core insulation PVC compound

Core identification Positive conductor: green

Negative conductor: white

Core layering Cores twisted together

Screening aluminium cladded plastic foil with tinned copper drain wire (7x0,30 mm)

Outer sheath PVC compound, colour: green

Electrical properties

Limiting deviation class 2 \pm 100 μ V (\pm 2,5 $^{\circ}$ C) / m easuring point temperature +900 $^{\circ}$ C

Mechanical and thermal properties

Temperature range occasional flexing: -5 ℃ up to +70 ℃

Minimum bending radius occasional flexing: 15 x cable diameter

Flammability flame retardant in acc. to IEC 60332-1-2 resp. VDE 0482-332-1-2