


REV.	DESCRIPTION	ENG.	APPROVAL



**NOTE:**

1.CABLE:DVI DIGITAL DUAL LINK CABLE,DV24M/DV24M 15u",UL20276,COLOR: GRAY

2.LENGHT:1800mm

3.CONNECTORS:DVI24P×2PCS (BLACK INSULATOR)

4.MOLD:ASSEMBLED MODEL

5.SCREW:4×40 INCH SCREW×4PCS

6.CONTACTS:


DVI24P	1	2	3	3	4	5	6	7	9	10	11	11	12	13	17	18	19
DVI24P	1	2	3	3	4	5	6	7	9	10	11	11	12	13	17	18	19
	TWIST		SHIELD	SHIELD	TWIST		TWIST	TWIST	TWIST		SHIELD	SHIELD	TWIST		TWIST		SHIELD

19	20	21	22	23	24	14	15	16	64
19	20	21	22	23	24	14	15	16	64
SHIELD		TWIST		SHIELD	TWIST		28AWG		

7.CARTON:K=A,501×300×300MM

8.PACKING:1PC/"MANHATTAN" CABLE ZIPBAG(3)+  
+ BARCODE STICKER

9.OPEN/SHDRT TEST:100% TEST. INSULATION:MIN.2M.



LABEL-328838

ICT PART NUMBER:ICOC DVI-8100-065  
REFERENCE PART#:ICOC DVI8100

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF INTRACOM Asia Co.,Ltd. AND SHALL NOT BE REPRODUCED COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF INTRACOM Asia Co.,Ltd.

**INTRACOM** 安達康股份有限公司  
INTRACOM Asia Co.,LTD.

UNLESS OTHERWISE SPECIFIED:DIMENSIONS ARE IN MILLIMETERS ANGULAR TOLERANCE:±1.0

DIMENSIONS	TOLERANCE
0.00 TO 30.00mm	±0.10mm
30.01 TO 80.00mm	±0.13mm
80.01 TO 150.00mm	±0.15mm
150.01	±0.20mm

MATERIAL

APPD.	REVD.
CUSTOMER.	CHKD.
SCALE. /	UNIT. mm
DR. FISH SHENG 10/9/03	
TITLE. ICOC DVI-8100	
BARCODE NO. 328838	SIZE. A4
FILE NAME. ICT03-09-10-01	SHEET 1/1
REV.	A