1. Engineering Change Notice

Date	Signature	Revision	Descriptions
2012-6-27	GINO	А	Initial release.
2012-6-28	GINO	Α	Add lengths description

2.Scope & General Specification

2.1 Extent of Application

This specification apply to

cable Assembly.

2.2 Appearance & Size

Shall be shown in Figure 3.1 which is to apply this specification

2.3 Working temperature & humidity

Advise :Upper service temperature is 40°C, Lower service temperature is 0°C;humidity<90%RH

2.4 Storage temperature & humidity

Advise: Upper service temperature is 30°C, Lower service temperature is 10°C; humidity<80%RH.

	Length		REVISION		
	100.5	REV	DESCRIPTION	DATE	SIGNATURE
	100±5mm	<	Initial release	2012.06.27	GINO
		M-1	Add lengths description	_01068	GINO
		1 7 7 7 7 7 7 7 7 7 7 7 7 7 7 7 7 7 7 7			
		rengui			
				2	
\@ \\@					
Cond	Conductor: 14/0.07 Enamelled Wire DFC x3C+kevlar	Wire OFC x3C+k	evlar		
	,Red/green/natu	9 7.			
			Red		
			•		
ADOUT ADOUT	Jacket: PVC, white		Nature		
M3.0±0.1mm——			Green		
Cable construction			3.5 SP(M)	3.5 SP(M)	(M)
			Wiring	Wiring Method	

GIN0 2012. 06. 27

DRAWN BY

CHECKED BY

SCALE TOL UNLESS NOTED APPROVED BY

UNIT

+0.1

free

шш

Ni-plated FINISH

brass

QTY

Silver White

AL PE

Shell

335-001-2 S00-031

600

2 2 2

Inner molding 3.5SP(M) Plug

COMPONENTS

(1) 335–001 No PART No.

3. 5SP(M) - 3. 5SP(M)

TITLE

DRAWING No. 169011101001

SHEET