



DATA SHEET	0163022
IEC compensating cable KP 15 L-SIL 2x1,5 round	valid from : 01.12.2008

Application

The compensating cable KP 15 L-SIL 2 x 1,5 mm² is a silicone insulated cable which transmits the thermoelectric voltage of PtRh/Pt thermocouples. It is for flexible use and fixed installation in dry and damp rooms without mechanical load. They may only be installed outdoors with UV protection and in observation of the max. permitted temperature range.

Design

Conductor	1,5 mm ² (48 x 0,20 mm)
Conductor material	RCB/SCB alloying, accuracy class 2 according IEC 60584 Positive conductor: Cu (copper) Negative conductor: CuNi (cupronickel)
Core insulation	Silicone compound
Core identification	Positive conductor: orange Negative conductor: white
Core layering	Cores twisted together
Outer sheath	Silicone compound, colour: orange

Electrical properties

Limiting deviation class 2	± 60 µV (± 5,0 °C) / measuring point temperature +1000 °C
----------------------------	---

Mechanical and thermal properties

Temperature range	occasional flexing: -25 °C up to +180 °C
Minimum bending radius	occasional flexing: 12 x cable diameter
Flammability	flame retardant in acc. to IEC 60332-1-2 resp. VDE 0482-332-1-2

Originator: Frank Hörtnagl / PD-KL Approved: Werner Körner / TE	Document: DB0163022EN	page 1 of 1
--	-----------------------	-------------

All deviations from this specification are subject to explicit consent of U.I.LAPP GmbH. All rights reserved acc. to DIN 34.
No.: 0019/0408