



DATA SHEET	0163051
IEC compensating cable KP 9-022 L 2x0,22	valid from : 01.12.2008

Application

The compensating cable KP 9-022 L 2 x 0,22 mm² is a PVC insulated cable which transmits the thermoelectric voltage of PtRh/Pt thermocouples. It is for flexible use and fixed installation in dry and damp rooms. They may only be installed outdoors with UV protection and in observation of the max. permitted temperature range.

Design

Conductor	0,22 mm ² (7 x 0,20 mm)
Conductor material	RCB/SCB alloying, accuracy class 2 according IEC 60584 Positive conductor: Cu (copper) Negative conductor: CuNi (cupronickel)
Core insulation	PVC compound
Core identification	Positive conductor: red Negative conductor: white
Core layering	Cores twisted together
Outer sheath	PVC compound, colour: white

Electrical properties

Limiting deviation class 2 ± 60 µV (± 5,0 °C) / measuring point temperature +1000 °C

Mechanical and thermal properties

Temperature range	occasional flexing: -5 °C up to +70 °C
Minimum bending radius	occasional flexing: 12 x cable diameter
Flammability	flame retardant in acc. to IEC 60332-1-2 resp. VDE 0482-332-1-2

Originator: Frank Hörtnagl / PD-KL Approved: Werner Körner / TE	Document: DB0163051EN	page 1 of 1
--	----------------------------	-------------