


U.I. Lapp GmbH	<b>DATASHEET</b>	 <b>LAPP GROUP</b>
	<b>EPIC® MC Module: High Voltage 4+PE</b>	<b>10383300</b> <b>14.11.2013</b>

The mixed assembly guarantees high flexibility. For applications in mechanical and plant engineering, for printing machines and slide-in technology.

The mix of different functions in one plug guarantees high flexibility

Assembly of individual connectors, suitable for different applications



Automation



Industrial machinery and plant engineering



Wind Energy



#### Info

Power and signal modules can be used together in one housing

#### Application range

Plant engineering

Printing machines

Control engineering


#### Remark

Photographs are not to scale and do not represent detailed images of the respective products.

#### Technical Data


Article:	MCB 5 CG
Version:	female
Contacts:	4 + PE
Pieces / PU:	10
Rated voltage (V):	1000 V
Rated current (A):	16 A
Contact resistance:	< 2 mOhm
Contacts:	Copper alloy, hard silver-plated
Number of contacts:	4 + PE
Termination methods:	Crimp termination: 0.5 - 2.5 mm²
Cycle of mechanical operation:	100
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C
Degree of soiling:	3

Product Management	Document: EPIC® MC Module: High Voltage 4+PE	1 / 2
--------------------	--	-------


U.I. Lapp GmbH	<b>DATASHEET</b>	 <b>LAPP GROUP</b>
	<b>EPIC® MC Module: High Voltage 4+PE</b>	10383300 14.11.2013



M



F



Product Management	Document: EPIC® MC Module: High Voltage 4+PE	2 / 2
--------------------	--	-------