

U.I. Lapp GmbH	<h1>DATASHEET</h1>	
	<b>EPIC® MC Module: PROFIBUS DP</b>	10390400 14.11.2013

The mixed assembly guarantees high flexibility. For applications in mechanical and plant engineering, for printing machines and slide-in technology.

Uninterruptible fieldbus operation when pulling the connector

Transmission rate up to 12 MBit/s

Easy assembly by screw connection

Shielding connection by strain relief



Automation



Industrial machinery and plant engineering



Wind Energy



### Info

Profibus DP module for uninterrupted fieldbus operation

### Application range

Plant engineering

Light & sound technology

Control engineering

### Remark

Photographs are not to scale and do not represent detailed images of the respective products.

### Technical Data


Article:	MCS 2 SS
Version:	male
Contacts:	2 + shield
Pieces / PU:	5
Rated voltage (V):	30 V
Rated current (A):	1 A
Contacts:	Copper alloy, gold-plated
Number of contacts:	2 / 4 + shield
Termination methods:	Screw termination: for Profibus cable
Cycle of mechanical operation:	100
Temperature range:	-20 °C až +85 °C
Degree of soiling:	3

Product Management	Document: EPIC® MC Module: PROFIBUS DP	1 / 2
--------------------	--	-------


U.I. Lapp GmbH	<b>DATASHEET</b>	 <b>LAPP GROUP</b>
	<b>EPIC® MC Module: PROFIBUS DP</b>	10390400 14.11.2013



**M**



**F**



Product Management	Document: EPIC® MC Module: PROFIBUS DP	2 / 2
--------------------	--	-------