

VS182 / VS184

2/4-Port HDMI Splitter

The VS182 / VS184 HDMI Splitter is the perfect solution for anyone who needs to send one source of digital high-definition video to two (VS182) or four (VS184) displays at the same time. It supports all HDMI-enabled equipment, such as DVD players, satellite set-top boxes and all HDMI displays.

The VS182 / VS184 HDMI Splitter is HDCP (High Bandwidth Digital Content Protection) compliant, making it effective for use with all HDMI displays in home theater applications, as well as in corporate, educational and commercial settings.




Maintains High-Definition Resolution up to 1080p!

HDMI™
HIGH DEFINITION MULTIMEDIA INTERFACE



Setup



Features

- Connects one HDMI A/V source to two (VS182) or four (VS184) HDMI displays at the same time
- Superior video quality – HDTV resolution of 480p, 720p, 1080i and 1080p (1920x1080); VGA, SVGA, SXGA, UXGA (1600x1200), WUXGA (1920x1200)
- Cascade distance: Source to Device -1.8m, Device to Device-15m, Device to Display-20m
- HDMI (Deep color)
- Cascadable to 3 levels - provides up to 8 / 64 HDMI signals.
- Long distance transmission – 20 m (24 AWG)
- DDC compatible
- HDMI and HDCP 1.1 compatible
- Signaling rates up to 2.25Gbits in support of 1080p display
- All-metal casing
- LED indication of display devices
- Plug-and-play – no software installation required
- Easy and affordable way to take your home theater system to the next level, or upgrade presentations, training, and video broadcasts in a corporate, educational, or commercial setting.

Specifications

Function		VS182	VS184
Display Connections		2	4
Connectors	Device	1 x HDMI Type A Female (Black)	
	Display	2 x HDMI Type A Female (Black)	
Power Jack		1 x DC Jack	
LEDs	Power	1 (Orange)	
	Input	1 (Green)	
	Output 1	1 (Green)	
	Output 2	1 (Green)	
	Output 3	N/A	1 (Green)
HDMI Resolution		HDTV resolutions up to 1080p, computer resolutions up to WUXGA(1920x1200)	
Power Consumption		DC5.3V, 2.0W	DC5.3V, 4.6W
Environment	Operating Temp.	0-50°C	
	Storage Temp.	-20°C-60°C	
	Humidity	0-80% RH, Non-condensing	
Physical Properties	Housing	Metal	
	Weight	0.31 kg	0.47 kg
	Dimensions (LxW xH)	12.50 x 8.15 x 2.50 cm	20.00 x 8.00 x 2.50 cm

* The specifications and pictures are subject to change without notice.