DATA SHEET



ÖLFLEX[®] 150 CY

DB 0015703 valid from: 2014-03-11

Application

ÖLFLEX[®] 150 CY cables are oil resistant power and control cables designed for the European, North American and Canadian market, for occasional flexible use and fixed installation subject to normal mechanical load conditions. They are among others designed for use in dry, damp and wet rooms. Outdoor use: They may only be installed with UV protection and considering the temperature range. ÖLFLEX[®] 150 CY cables are increased oil resistant and at room temperature they are widely resistant to acids and caustic solutions. They are suitable for non-continuously recurring movement without tensile load. Continuous operational movements, restricted guidance, usage of these cables in moving cable carriers or on motor drum guidance or under a strain of more than 15 N/mm² are not allowed.

Application range: Plant engineering, industrial machinery, heating and air-conditioning systems Application range:

plant engineering, industrial machinery, heating and air conditioning systems

HAR:	DIN VDE 0298-300 resp. VDE 0298-300
acc. to UL:	PVC-sheathed cables for external interconnection or internal wiring of electric and electronic equipment,
	Use when getting in contact with oil not above +60 °C (60 °C oil rating)
acc. CSA:	CSA AWM I A/B II A/B, cables for internal or external interconnection with or without mechanical load

Design

Design	≤ 61 cores: acc. to EN 50525-2-51 resp. VDE 0285-525-2-51 > 61 cores: based on EN 50525-2-51 resp. VDE 0285-525-2-51 UL AWM Style 21098 or 2587, CSA C22.2 No. 210-11
Approvals	UL AWM Style 21098 or 2587 (File No. E63634) CSA AWM I A/B II A/B (File No. LL 53776) ≤ 61 cores: acc. to H05VVC4V5 acc. to EN 50525-2-51 resp. VDE 0285-525-2-51 > 61 cores: based on EN 50525-2-51 resp. VDE 0285-525-2-51
Conductor	fine wire strands of bare copper, acc. to IEC 60228 resp. VDE 0295, Class 5
Core insulation	PVC compound TI2 acc. to DIN EN 50363-3 resp. VDE 0207-363-3 (UL/CSA 90°C rating)
Core identification	acc. to VDE 0293-1, with or without GN/YE ground conductor black cores with white numbers acc. to DIN EN 50334 resp. VDE 0293-334
Inner sheath	PVC compound TM 2 acc. to DIN EN 50363-4-1 resp. VDE 0207-363-4-1 (UL/CSA 90°C rating)
Screen	braid of tinned copper, coverage = 85 % (nominal value)
Outer sheath	PVC compound TM5 acc. to DIN EN 50363-4-1 resp. VDE 0207-363-4-1 (UL/CSA 90°C rating) colour: silver grey, similar RAL 7001

Electrical properties

Nominal voltage	U_0/U in acc. to HAR: U acc. to UL / CSA:	300 / 500 V 600 V
Test voltage	core / core core / screen	3000 V AC 3000 V AC

Originator: KASC / PDC approved: HAPF / PDC	Document:	DB0015703EN	Page 1 of 2
All rights reserved acc. to DIN ISO 16016. PD 0019/2.2_11.10EN			





ÖLFLEX[®] 150 CY

DB 0015703 valid from: 2014-03-11

Mechanical and thermal properties

Min. bending radius	occasional flexing: fixed installation:	20 x outer diameter 6 x outer diameter
Temperature range	occasional flexing:	acc. to HAR-5 °C up to +70 °C max. conductor temp.acc. to UL / CSA-5 °C up to +90 °C max. conductor temp.
	fixed installation:	acc. to HAR -40 °C up to +70 °C max. conductor temp. acc. to UL / CSA -40 °C up to +90 °C max. conductor temp.
Oil resistance	TM 5 acc. to DIN EN 503	63-4-1 resp. VDE 0207-363-4-1
Flammability	HAR: acc. to IEC 6033 UL: vertical flame tea CSA: FT1	32-1-2 resp. VDE 0482-332-1-2 st VW-1
Tests	acc. to IEC 60811, EN 50	395, EN 50396, UL 1581and CSA 22.2
EC-Directives		he EC-Directives 2006/95/EC (Low Voltage Directive) , Restriction of the use of certain hazardous substances).

Originator: KASC / PDC		
approved:	HAPF / PDC	