

VOLTCRAFT®

VOLTCRAFT® - TOP PERFORMANCE IN EVERY WAY

"Since 1982, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success."

PL-125-T2 DIGITAL THERMOMETER

CE

VERSION 12/21

Nº 1012836

Robust thermometer with soft rubber cover for type K and type J thermocouples. The large, lighted display and the function buttons at the side enable ergonomic handling. The integrated real-time clock allows reading the MIN/MAX/AVG values with timestamps, which makes monitoring in a long period significantly easier. Besides the provided wire sensor (one unit per channel), all type K and type J temperature sensors can be connected with miniature thermocouple plug.

FEATURES:

2 channels // For thermocouples type K/J //
MAX/MIN/AVG with time stamps //
Data logger for 18000 readings // USB port //

EQUIPMENT:

Temperature display in °C, °F or K // Auto Power-Off
function // Differential measurement (T1-T2).

PACKAGE CONTENTS:

PL-125-T2 // 2x type K wire sensors (-20 to +250 °C) //
3 batteries (AAA) // USB cable // Voltsoft Standard
Software-CD // Operating instructions.

TECHNICAL DATA:

Model:	2 Channel
Temperature range:	Type K: -200 to +1372 °C
Type J: -210 to +1100 °C	0.2 V - 500 V
Resolution temperature:	0.1 °C
Basic accuracy	±0.1 (0.15% + 1 °C)
Sensor type	K/J
Port:	USB
Power supply:	3 micro batteries (AAA)
Dimensions (W x H x L):	62 x 28 x 162 mm
Weight:	184 g



Legal notice

This data sheet is published by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).
All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited.
This data sheet represent the technical status at the time of printing.

© Copyright 2022 by Conrad Electronic SE

1012836_V4_1221_01_PIX_ds