DATA SHEET



ÖLFLEX[®] 191

DB 0011113 valid from: 2013-11-08

Application

ÖLFLEX[®] 191 cables are oil resistant control cables for the European, Northern American and Canadian market for occasional flexible use and fixed installation subject to normal mechanical load conditions. They are among others designed for use in dry, damp and wet conditions. Outdoor use: They may only be installed with UV protection and considering the temperature range. ÖLFLEX® 191 cables are increased oil resistant and at room temperature widely resistant against acid and caustic solutions. They are suitable for non-continuously recurring movement without tensile load. Continuous operational movements, restricted guidance, usage of these cables in moving cable carriers or on motor drum guidance or under a strain of more than 15 N/mm² are not allowed.

Application range: Plant engineering, industrial machinery, heating and air-conditioning systems

USE according to UL:	PVC sheathed cables for external interconnection or internal wiring of electronic equipment,
	appliances where exposed to oil at a temperature not exceeding 80° C
USE according to CSA:	I A/B and II A/B. Cables for internal wiring or external interconnection with or without
	mechanical abuse

Design

Design	acc. to	UL 758; Style 10012 and 21098 CSA AWM C22.2 No. 210-11
	based on	DIN EN 50525-2-51/ VDE 0285-525-2-51
Approval	UL CSA	UL AWM, Style 10012 and 21098 or 2587 (File No. 63634) AWM I A/B, II A/B (File No. LL 53776)
Conductor	fine wire strands of bare copper, acc. to IEC 60228 resp. VDE 0295, Class 5	
Core insulation	PVC compound (UL/CSA 90°C rating)	
Core identification	acc. to VDE 0293-1, with or without GN/YE ground conductor black cores with white numbers acc. to DIN EN 50334 resp. VDE 0293-334	
Outer sheath	PVC compound ((UL / CSA 90°C Rating) Colour: silver grey, similar RAL 7001	

Electrical properties

Nominal voltage	VDE: UL/CSA	U ₀ /U	300 / 500 V 600 V
Test voltage	C / C		<u>></u> 4000 V AC
Specific insulation resistance	> 20 GΩ x cm		

Mechanical and thermal properties

Min. bending radius	occasional flexing: fixed installation:	20 x outer diameter 6 x outer diameter
Temperature range	occasional flexing (VDE): occasional flexing (UL/CSA): fixed installation (VDE): fixed installation (UL/CSA):	 -5 °C up to +70 °C max. conductor temp. -5 °C up to +90 °C max. conductor temp. -40 °C up to +70 °C max. conductor temp. -40 °C up to +90 °C max. conductor temp.

Originator:	KASC/ PDC	Document:		
Approved:	HAPF / PDC		DB0011113EN	page 1 of 2
All rights reserved ago to DIN ISO 16016				

DATA SHEET



ÖLFLEX[®] 191

DB 0011113 valid from: 2013-11-08

Oil resistance	VDE: EN 50363-4-2 resp. VDE 0472-363-4-1 UL: 80°C rating acc. to. UL 758 CSA: acc. to CSA C22.2 No. 210-11	
Flammability	flame retardant in acc. with IEC 60332-1-2 resp. VDE 0482-332-1-2 UL: Cable flame test, VW-1 CSA: FT1	
Tests	acc. to IEC 60811, EN 50395, EN 50396	
EC-Directives	This cable is conform to the EC-Directives 2006/95/EC (Low Voltage Directive) and 2011/65/EU (RoHS, Restriction of the use of certain hazardous substances).	

 Originator:
 KASC/PDC
 Document:
 DB0011113EN
 page 2 of 2