

U.I. Lapp GmbH	DATASHEET	
	TEC sealing cap	61830040 14.11.2013

TEC sealing caps with adhesive coating inside can be used for insulating and sealing of cable splices.



Good chemical resistance



Halogen-free



UV-resistant



Waterproof

Application range

For sealing cable ends against the seepage of moisture and contaminants

Benefits

Secure sealing through thermoplastic adhesive coating on the inside
 Good resistance to chemicals and solvents
 Ensures high tensile strength and mechanical protection

Norm references / Approvals

Protection rating: IP67

Remark

1. after shrinking +/- 10%; 2. after shrinking +/- 20%

Photographs are not to scale and do not represent detailed images of the respective products.

Product Management	Document: TEC sealing cap	1 / 3
--------------------	---------------------------	-------


U.I. Lapp GmbH	DATASHEET	
	TEC sealing cap	61830040 14.11.2013

Technical Data

Article description:	TEC 55/25
H max. mm:	55
H min. mm:	25
J max. mm:	16
Cable Ø (mm):	28 - 47
R* after shrinking (mm):	130
Panel thickness HW* (mm):	3.3
Pieces / PU:	10
General:	UV-resistant Double-walled
Colour delivered:	Black
Material:	Cross-linked modified polyolefin, with thermoplastic adhesive coating inside Halogen-free and silicone-free
Temperature range:	-55°C to +100 °C Shrink temperature: 135°C

Product Management	Document: TEC sealing cap	2 / 3
--------------------	---------------------------	-------

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	TEC sealing cap	61830040 14.11.2013



Product Management	Document: TEC sealing cap	3 / 3
--------------------	---------------------------	-------