

U.I. Lapp GmbH	<h1>DATASHEET</h1>	
	Conductor end sleeves insulated	61801650 14.11.2013

Conductor end sleeves with insulation for cabinet builders , according to DIN or German colour code, CSA approved, halogen-free



Halogen-free



Application range

Control cabinets and equipment wiring

Benefits

Funnel-shaped opening makes it easy to slip them onto the strands
The conductor is permanently connected to the collar by crimping

Norm references / Approvals

All DIN conductor end-sleeves are in accordance with DIN 46228 Part 4
CSA approved, File-Number: LR 105629-1

Remark

K = short; N = medium; HL = large; L = extra large; Other sizes and colours are available upon request
Photographs are not to scale and do not represent detailed images of the respective products.

*Under some circumstances the end sleeves withstand temperatures under -5°C. Please contact Lapp Kabel to clarify the specific application area.

Technical Data

Article designation:	AHI DIN L 0,75/12
For mm ² :	0,75
AWG:	20
Colour:	grey
l1 mm:	18
l2 mm:	12
d 1 mm:	1.3
s1 mm:	0.15
d 2 mm:	2.8
s2 mm:	0.25
Pieces / PU:	500
Note:	Halogen-free
Material:	Copper/PP Surface: tin-plated
Temperature range:	-5°C to +105°C*

Product Management	Document: Conductor end sleeves insulated	1 / 2
--------------------	---	-------

U.I. Lapp GmbH	<h1>DATASHEET</h1>	 LAPP GROUP
	Conductor end sleeves insulated	61801650 14.11.2013



Product Management	Document: Conductor end sleeves insulated	2 / 2
--------------------	---	-------