

U.I. Lapp GmbH	<b>DATASHEET</b>	
	<b>Conductor end sleeves insulated</b>	61801710 14.11.2013

Conductor end sleeves with insulation for cabinet builders , according to DIN or German colour code, CSA approved, halogen-free



Halogen-free



### Application range

Control cabinets and equipment wiring

### Benefits

Funnel-shaped opening makes it easy to slip them onto the strands  
The conductor is permanently connected to the collar by crimping

### Norm references / Approvals

All DIN conductor end-sleeves are in accordance with DIN 46228 Part 4  
CSA approved, File-Number: LR 105629-1

### Remark

K = short; N = medium; HL = large; L = extra large; Other sizes and colours are available upon request  
Photographs are not to scale and do not represent detailed images of the respective products.


\*Under some circumstances the end sleeves withstand temperatures under -5°C. Please contact Lapp Kabel to clarify the specific application area.

### Technical Data

Article designation:	AHI DIN N 1,5/8
For mm <sup>2</sup> :	1,5
AWG:	16
Colour:	black
l1 mm:	14.5
l2 mm:	8
d 1 mm:	1.8
s1 mm:	0.15
d 2 mm:	3.4
s2 mm:	0.3
Pieces / PU:	500
Note:	Halogen-free
Material:	Copper/PP Surface: tin-plated
Temperature range:	-5°C to +105°C*

Product Management	Document: Conductor end sleeves insulated	1 / 2
--------------------	---	-------

U.I. Lapp GmbH	<h1>DATASHEET</h1>	 <b>LAPP GROUP</b>
	<b>Conductor end sleeves insulated</b>	<b>61801710</b> <b>14.11.2013</b>



Product Management	Document: Conductor end sleeves insulated	2 / 2
--------------------	---	-------