


U.I. Lapp GmbH	<b>DATASHEET</b>	
	<b>Conductor end sleeves AHK, insulated</b>	61746501 14.11.2013

Insulated conductor end sleeves for short circuit cables up to 3 kV, For cables with thick insulation



Halogen-free

### Application range

For cables with thick insulation

Special conductor end sleeve model with large plastic collar for thick insulation cables (e.g. NSGAFÖU).

Suitable for unprotected connections on control and distribution panels, rail vehicles, solar systems, ignition cables etc.

### Benefits

Thicker insulation and greater wall thickness for higher loads

Suitable for all short circuit and earth fault-resistant cables up to 3 kV due to enlarged insulation sleeves

### Note

For processing tools see the keyword index "crimping pliers for conductor end sleeves"

### Remark

Photographs are not to scale and do not represent detailed images of the respective products.

### Technical Data

Article designation:	AHK 1,5/10
For mm <sup>2</sup> :	1,5
AWG:	16
Colour:	black
l1 mm:	19.5
l2 mm:	10
d 1 mm:	1.8
s1 mm:	0.15
d 2 mm:	7.5
s2 mm:	0.3
Pieces / PU:	100
Material:	Copper/PP Surface: tin-plated
Temperature range:	-5°C to +105°C

Product Management	Document: Conductor end sleeves AHK, insulated	1 / 2
--------------------	------------------------------------------------	-------

U.I. Lapp GmbH	<h1>DATASHEET</h1>	 <b>LAPP GROUP</b>
	<b>Conductor end sleeves AHK, insulated</b>	<b>61746501</b> <b>14.11.2013</b>



Product Management	Document: Conductor end sleeves AHK, insulated	2 / 2
--------------------	------------------------------------------------	-------