


U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	ÖLFLEX® CONTROL TM CY	281605CY 14.11.2013

Wide application range due to multiple approvals

Cost-saving, easy installation due to omission of closed raceways (suitable for open wiring)



Flame-retardant



Cold-resistant



Mechanical resistance



Oil-resistant



Interference signals



Torsion-resistant

Info

Torsion resistant for drip loops

Wide application range (NFPA 70/NEC)/ compliance with NFPA 79 for industrial machinery

EMC/Screened

Application range

Industrial machinery; plant engineering

Machine tools compliant with UL MTW (Machine Tool Wiring)

TC-ER (Tray Cable Exposed Run) approval for open wiring between cable tray and industrial machines/plants acc. to NEC 336.10(7)

Wind turbines: USA Wind Turbine Tray Cable (WTTC)

Class 1, Div. 2 in accordance with NEC "National Electrical Code" Art. 336, 392, 501

Design

Fine-wire strand made of bare copper wires


Insulation: PVC with nylon sheath (PA skin)

Aluminum-coated foil

Tinned-copper braiding

Outer sheath made of special PVC compound, grey

Product Management	Document: ÖLFLEX® CONTROL TM CY	1 / 2
--------------------	---------------------------------	-------

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	ÖLFLEX® CONTROL TM CY	281605CY 14.11.2013

Norm references / Approvals

Multi-standard cables have conductor strands with nominal sizes in mm² or AWG/kcmil. The master size is mentioned in the table below, while the equivalent size of the other system can be found in the Appendix T16 of this catalogue. For this related secondary size the cross-section of the conductor mostly works out to be greater than the specified nominal value.

Cable type certifications UL MTW, TC-ER, WTTC 1000 V, BUS DROP, c(UL) Type TC, CIC FT4, CSA AWM I/II A/B FT4, UL AWM style 20886

Product features

Flame-retardant according to CSA FT4 UL Vertical-Tray Flame Test

Oil-resistant according to UL OIL RES I & II

Water-resistant, UL Wet Approval 75 °C

High degree of screening low transfer impedance (max. 250 Ω/km at 30 MHz)

Suitable for torsional applications which are typical for the loop in wind turbine generators (WTG)

Remark

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

Packaging size: coil ≤ 30 kg or ≤ 250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 610 m drum or 8 x 76 m coils).

Photographs are not to scale and do not represent detailed images of the respective products.

*OD = Outer diameter

Technical Data

Number of cores and mm ² per conductor:	5 G 1,5
Outer diameter (mm):	10,2
Copper index (kg/km):	99.1
Weight (kg/km):	189
Core identification code:	Black with white numbers
Classification:	ETIM 5.0 Class-ID: EC000104 ETIM 5.0 Class-Description: Control cable
Conductor stranding:	Fine-wire, bare copper strand
Torsion movement in WTG:	TW-0 & TW-2, refer to Appendix T0
Minimum bending radius:	Static/Occ. moved: 5/20xOD*
Nominal voltage:	UL/CSA: 600 V (TC, MTW, CIC), WTTC 1000 V UL/CSA: 1000 V (AWM) VDE U0 /U: 600/1000 V
Test voltage:	2000 V
Protective conductor:	G = with GN-YE protective conductor X = without protective conductor
Temperature range:	-40 °C (static)/ -25 °C (occ. moved) to +90 °C (AWM: +105 °C)

Product Management	Document: ÖLFLEX® CONTROL TM CY	2 / 2
--------------------	---------------------------------	-------