

U.I. Lapp GmbH	<h1>DATASHEET</h1>	
	EPIC® MC Module: Koax 3pole	10399300 14.11.2013

The mixed assembly guarantees high flexibility. For applications in mechanical and plant engineering, for printing machines and slide-in technology.

The mix of different functions in one plug guarantees high flexibility

Assembly of individual connectors, suitable for different applications



Automation



Industrial machinery and plant engineering



Wind Energy



Info

RGB video signal transmission in one module

Application range

Plant engineering

Light & sound technology

Control engineering

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data


Article:	MCB 3 coax
Version:	female
Contacts:	3
Pieces / PU:	10
Rated voltage (V):	250 V
Contact resistance:	< 2,7 mOhm
Contacts:	Copper alloy, gold-plated
Number of contacts:	3
Termination methods:	Solder termination: var. coax cables
Cycle of mechanical operation:	100
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C
Degree of soiling:	3

Product Management	Document: EPIC® MC Module: Koax 3pole	1 / 2
--------------------	---------------------------------------	-------


U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	EPIC® MC Module: Koax 3pole	10399300 14.11.2013



M



F



Product Management	Document: EPIC® MC Module: Koax 3pole	2 / 2
--------------------	---------------------------------------	-------