

| | | |
|-------------------|-------------------------------------|--|
| U.I. Lapp GmbH | DATASHEET |  |
| | Tube cable lugs KR/ KRT/ KRF | 61803300 14.11.2013 |

Tube cable lugs KR/KRT/KRF, also for fine.wire copper conductors, class 2 and 5, tinned electrolyte copper, with inspection hole, for railway industry



Application range

KR: For fine and multi-wire copper conductors (class 2 and 5) with a cross-sectional range of 0.75 -10.00 mm²

KRT: For multi-wire copper conductors (class 2)with a cross-sectional range of 10 - 400 mm²

KRF: For fine wire copper conductors (class 2 and 5) with a cross-sectional range of 16 - 400 mm²

Mainly for connection to rails and to copper connectors

Max. 48 kW

Benefits

With inspection hole (from size 10 mm² on, KR beginning 4 mm²)

High-quality electrolytic copper ensures a good crimping quality

Norm references / Approvals

In combination with recommended crimp tool fulfill requirements of SEN 245010, BS 4579:1, VDE 0220:1, EN-IEC 61238:1

UL file number: E205350 (see table)

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

| | |
|----------------------|--|
| Article designation: | KRF 150/12 |
| Screw hole Ø (mm): | 12 |
| UL approval: | yes |
| Length (mm): | 80 |
| Pressing dies: | B 25/13 B 25 |
| d mm: | 19 |
| W mm: | 36 |
| Pieces / PU: | 25 |
| Material: | Tinned electrolyte copper |
| Temperature range: | Temperature range up to +90°C Working temperature: 110°C, max. +140°C |

| | | |
|--------------------|--|-------|
| Product Management | Document: Tube cable lugs KR/ KRT/ KRF | 1 / 1 |
|--------------------|--|-------|