


U.I. Lapp GmbH	<h1>DATASHEET</h1>	
	EPIC® MC Module: High Current 2pole	10345100 29.11.2013

The mixed assembly guarantees high flexibility. For applications in mechanical and plant engineering, for printing machines and slide-in technology.

The mix of different functions in one plug guarantees high flexibility

Screw connection up to 25mm² for easy assembly without special tools



Automation



Industrial machinery and plant engineering



Wind Energy

Info

High power module 2pole with screw connection

Application range

Plant engineering

Printing machines

Control engineering

Remark


Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data


Article:	MCB-HC 2
Version:	female
Contacts:	2
Rated voltage (V):	IEC: 1000 V UL: 600 V CSA: 600 V
Rated current (A):	82 A
Contact resistance:	< 2 mOhm
Contacts:	Copper alloy, hard silver-plated
Number of contacts:	2
Termination methods:	Screw termination: 10.0 - 25.0 mm ²
Cycle of mechanical operation:	100
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C
VDE-tested:	Certified production control: VDE-REG. no. A870
	UL-tested: UL File Number: E75770
Degree of soiling:	3

Product Management	Document: EPIC® MC Module: High Current 2pole	1 / 2
--------------------	---	-------


U.I. Lapp GmbH	<h1>DATASHEET</h1>	 LAPP GROUP
	EPIC® MC Module: High Current 2pole	10345100 29.11.2013



M



F



Product Management	Document: EPIC® MC Module: High Current 2pole	2 / 2
--------------------	---	-------