


U.I. Lapp GmbH	<b>DATASHEET</b>	
	<b>Panel connectors insulated</b>	<b>63103040</b> <b>14.11.2013</b>

Insulated panel connectors (type M T and V), UL approved, with Easy Entry Funnel Shape of the plastic sleeve



### Application range

For breaking through the oxidation layer on the conductor when crimping

### Benefits

For first-class connection with simple operating principle  
 Hard-soldered cable lug that can be pressed in any position  
 Thus providing the best electrical conductivity (least resistance)  
 No risk of bent and crushed cables

### Design

For higher tensile strength  
 For good strength and improved current conduction  
 Flat receptacle material in contact pressing is double-folded and hard-soldered  
 EASY-ENTRY funnel shape of the plastic sleeve enables simple, fast and safe insertion of the conductor  
 1 = push-on female terminal, type H 2 = push-on piggyback terminal, type T 3 = push-on male terminal, type M 4 = push-on female terminal (fully insulated), type V

### Norm references / Approvals

File Number E334111, see table

### Remark

1 = PVC insulation, not easy-entry; 2 = polyamide (nylon) insulation, not easy-entry; 3 = unsoldered, with additional brass sleeve





Photographs are not to scale and do not represent detailed images of the respective products.

### Technical Data

Article designation:	L-RC 63 M
For mm <sup>2</sup> :	4 - 6
UL approval:	yes
Footnote:	1.3
Colour:	yellow
Blade connection:	6.3 x 0.8
d mm:	6.3
L:	25
Pieces / PU:	100
Material:	Nickel-plated brass Polycarbonate insulation
Temperature range:	-40°C to +100°C

Product Management	Document: Panel connectors insulated	1 / 2
--------------------	--------------------------------------	-------

U.I. Lapp GmbH	<b>DATASHEET</b>	 <b>LAPP GROUP</b>
	<b>Panel connectors insulated</b>	63103040 14.11.2013



Product Management	Document: Panel connectors insulated	2 / 2
--------------------	--------------------------------------	-------