Enables the use of cable glands with smaller connection threads than the existing threaded holes
Glass fibre-reinforced for maximum mechanical stability



1

Space requirement

Application range
Machines
Devices
Housings

Design
PG connection thread

Design
SKINDICHT® KU with hexagon and flat design
SKINDICHT® KUS with hexagon and larger height
SKINDICHT® KUK with knurled heads

Remark
Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article designation / sizeOuter / inner:	KUS 13,5/11
Pieces / PU:	50
Colour delivered:	Light grey (RAL 7035)
Material:	Polyamide, glass fibre-reinforced
Temperature range:	KU, KUS: -40°C to +100°C KUK: -20°C to +80°C

PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.

2

3

PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.