DATASHEET



EPIC® H-B 10 TSH

70052600 14.11.2013

Housing design H-B. The industry standard.

The smallest housing with single and double lever. The right housing is available for every application





Automation



Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

Info

Universal, robust metal housings size H-B 10

Application range

Plant engineering Light & sound technology Plastics industry

Product features

Hood, high version Bolts for double lever Side cable entry Versions with / without neck

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article:	H-B 10 TSH 29
PG:	29
Neck:	yes
Pieces / PU:	10
Material:	Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched)
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

LPIG®
-
6

Product Management	Document: EPIC® H-B 10 TSH	1 / 2
PN 0486/01_03.10 Photographs are not to scale and do not represent	©2012 Lapp Group - Technical changes reserved detailed images of the respective products.	


DATASHEET



EPIC® H-B 10 TSH

70052600 14.11.2013





Product Management	Document: EPIC® H-B 10 TSH	2/2
PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved Photographs are not to scale and do not represent detailed images of the respective products.		