

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINDICHT® MR-M hexagonal	52006572 14.11.2013

Enables the use of cable glands with smaller connection threads than the existing threaded holes
 With guide notch for O-ring
 Assembling with a wrench



Space requirement

Application range

Machines
 Devices
 Housings

Design

Metric connection thread acc. to EN 50262

Remark

Viton® is a registered trademark of DuPont de Nemours

Photographs are not to scale and do not represent detailed images of the respective products.


Technical Data

Thread, male M1:	80 x 2
Thread, female M2:	63 x 1.5
SW (mm):	85
Overall length, C (mm):	23
Thread length, D (mm):	15
Outer Ø (mm):	93,5
Pieces / PU:	1
On request:	VITON® O-ring -20 °C to +200 °C
Material:	Body: nickel-plated brass O-ring: NBR
Temperature range:	-30 °C to +100 °C



Product Management	Document: SKINDICHT® MR-M hexagonal	1 / 2
--------------------	-------------------------------------	-------

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINDICHT® MR-M hexagonal	52006572 14.11.2013



Product Management	Document: SKINDICHT® MR-M hexagonal	2 / 2
--------------------	-------------------------------------	-------