

U.I. Lapp GmbH	DATASHEET	
	SKINDICHT® SE-M without E+D	52108021 14.11.2013

Combination of different conduit glands is possible
Corrosion-resistant
Easy to install
Completely safe cable entry
Low overall height



Corrosion-resistant



Mechanical resistance



Space requirement



Connector with standard housing unit



Temperature-resistant

Application range

The flange angle gland can be combined with all glands (including O-ring) e.g. strain relief, bending protection and conduit glands

For high mechanical stress

When no connection thread is provided

Design

M20 x 1.5 - M25 x 1.5 with 2 screw holes M32 x 1.5 with 4 screw holes

Note

The protection class is dependent on the combination with the various special glands. The minimum standard is IP 55.

Cable glands are not included in scope of delivery

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Product Management	Document: SKINDICHT® SE-M without E+D	1 / 2
--------------------	---------------------------------------	-------

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINDICHT® SE-M without E+D	52108021 14.11.2013

Technical Data

Article designation / size:	32 x 1,5
Height (mm):	51,5
Overall width (mm):	66
Length (mm):	76
PU:	1
Material:	Body: zinc die-casting, grey, hammer tone finish O-ring: NBR
Protection rating:	IP 55
Temperature range:	-20°C to +100°C

Product Management	Document: SKINDICHT® SE-M without E+D	2 / 2
--------------------	---------------------------------------	-------