

U.I. Lapp GmbH	DATASHEET	
	EPIC® H-D 25 machined	11283300 14.11.2013

H-D inserts for stamped and machined crimp contacts

Inserts of the connector series H-D are designed for applications in which a high number of contacts are required.



Industrial machinery and plant engineering



Application range

Machine and equipment manufacturing
Control engineering

Remark


Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article:	H-D 25 SCM
Version:	male
Article designation:	machined
Contacts:	1 - 25
Pieces / PU:	5
Rated voltage (V):	IEC: 250 V UL: 250 V
Rated impulse voltage:	2.5 kV
Rated current (A):	IEC: 10 A UL: 10 A
Contact resistance:	< 2 mOhm
Contacts:	Copper alloy, hard silver/gold-plated
Number of contacts:	25 + PE
Termination methods:	Crimp termination: 0.14 - 2.5 mm ²
Cycle of mechanical operation:	100
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C
VDE-tested:	Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770
Degree of soiling:	3





Product Management	Document: EPIC® H-D 25 machined	1 / 2
--------------------	---------------------------------	-------

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	EPIC® H-D 25 machined	11283300 14.11.2013



M

F



Product Management	Document: EPIC® H-D 25 machined	2 / 2
--------------------	---------------------------------	-------