


U.I. Lapp GmbH	DATASHEET	
	EPIC® H-D 64 stamped	11271000 14.11.2013

H-D inserts for stamped and machined crimp contacts
 Inserts of the connector series H-D are designed for applications in which a high number of contacts are required.



Industrial machinery and plant engineering



Space requirement

Application range

Plant engineering
 Light & sound technology

Remark



Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article:	H-D 64 BCG
Version:	female
Article designation:	stamped
Contacts:	1 - 64
Pieces / PU:	5
Rated voltage (V):	IEC: 250 V UL: 250 V
Rated impulse voltage:	2.5 kV
Rated current (A):	IEC: 10 A UL: 10 A
Contact resistance:	< 2 mOhm
Contacts:	Copper alloy, hard silver/gold-plated
Number of contacts:	64 + PE
Termination methods:	Crimp termination: 0.14 - 2.5 mm ²
Cycle of mechanical operation:	100
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C
VDE-tested:	UL-tested: UL File Number: E75770
Degree of soiling:	3

Product Management	Document: EPIC® H-D 64 stamped	1 / 2
--------------------	--------------------------------	-------

U.I. Lapp GmbH	<h1>DATASHEET</h1>	
	EPIC® H-D 64 stamped	11271000 14.11.2013



Product Management	Document: EPIC® H-D 64 stamped	2 / 2
--------------------	--------------------------------	-------