

U.I. Lapp GmbH	DATASHEET	
	EPIC® H-D 7 stamped	11251000 14.11.2013

H-D inserts for stamped and machined crimp contacts
 Small, high-performance connector
 High performance crimping contacts
 PE contact with screw connection



Info

Compact, powerful standard insert
 Space saving, crimping contact

Application range

Machine and equipment manufacturing
 Control engineering

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data


Article:	H-D 7 BCG
Version:	female
Article designation:	stamped
Contacts:	1 - 7
Pieces / PU:	10
Rated voltage (V):	IEC: 24 V (AC)/60 V (DC) metal housing 250 V thermoplastic housing
	UL: 250 V
Rated impulse voltage:	2.5 kV
Rated current (A):	IEC: 10 A UL: 10 A
Contact resistance:	< 2 mOhm
Contacts:	Copper alloy, hard silver/gold-plated
Number of contacts:	7 + PE
Termination methods:	Crimp termination: 0.14 - 2.5 mm ²
Cycle of mechanical operation:	100
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C
VDE-tested:	Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770
Degree of soiling:	3

Product Management	Document: EPIC® H-D 7 stamped	1 / 2
--------------------	-------------------------------	-------



U.I. Lapp GmbH	DATASHEET	
	EPIC® H-D 7 stamped	11251000 14.11.2013





M




F



M



F



Product Management	Document: EPIC® H-D 7 stamped	2 / 2
--------------------	-------------------------------	-------