



U.I. Lapp GmbH	DATASHEET	
	SKINDICHT® SR	52001030 14.11.2013

Reliable bending and anti-kink protection
 High strain relief
 Robust
 For cables with large outer diameters
 High degree of protection



Wide clamping range



Optimum strain relief



Robust

Application range

Cables for electrical appliances and machinery that are moved under normal use must be protected against excessive bending as required in accordance with VDE 0700-1

Handheld device
 Portable equipment
 Building sites
 Moving machine parts

Design

PG connection thread

Note

Counter nut to be used: SKINDICHT® SM
 For EMC version, refer to SKINDICHT® SRE

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Product Management	Document: SKINDICHT® SR	1 / 3
--------------------	-------------------------	-------


U.I. Lapp GmbH	DATASHEET	
	SKINDICHT® SR	52001030 14.11.2013

Technical Data

Article designation / size:	SR 13/09
Clamping range ØF (mm):	7,5 - 9
Max. fitting size for installation (mm):	32
SW1/SW2 mm:	22 / 22
Overall length, C (mm):	62
Thread length, D (mm):	6.5
Pieces / PU:	25
Caution:	The installation dimensions can be found in appendix T21
On request:	Available with long connection thread
Material:	Body: nickel-plated brass O-ring: NBR Anti-kink protection: CR
Protection rating:	IP 65
Temperature range:	-20°C to +80°C

Product Management	Document: SKINDICHT® SR	2 / 3
--------------------	-------------------------	-------

U.I. Lapp GmbH	<h1>DATASHEET</h1>	 LAPP GROUP
	SKINDICHT® SR	52001030 14.11.2013



Product Management	Document: SKINDICHT® SR	3 / 3
--------------------	-------------------------	-------