


U.I. Lapp GmbH	<b>DATASHEET</b>	
	<b>J-Y(ST)Y...LG Indoor Cable</b>	<b>1591502</b> <b>14.11.2013</b>

Installation cable in accordance with DIN VDE 0815

Indoor telephone cables transmit analogue or digital signals

Aluminium-laminated plastic foil static screen with tin-plated drain wire minimises the interference of high frequency, electromagnetic fields

Decoupling of circuits by means of twisted-pair (TP) design (crosstalk effects)



Interference signals

### Application range

In news and communication applications, the following connections can be installed: telephone, telefax, telex, standard modems for postal services; burglar and fire alarm systems (cf. fire alarm cables); communication and paging systems; access control, time and data control systems

Can be used in dry and wet interiors for fixed installation on and under plaster

### Design

Solid bare copper conductor

Core insulation made of PVC

Cores twisted in pairs, pairs twisted together, foil wrapping over cable core, static screen made of aluminium-laminated plastic film with copper drain wire

Outer sheath made of PVC Outer sheath colour: pebble grey (RAL 7032)

### Norm references / Approvals

In accordance with DIN VDE 0815 type J-Y(ST)Y...LG

### Product features

The 2-paired versions = star quad cable design

Flame-retardant according IEC 60332-1-2

### Remark

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.


Copper price basis: EUR 100/100kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: [www.lappkabel.de/en/cable-standardlengths](http://www.lappkabel.de/en/cable-standardlengths)

Packaging size: coil  $\leq$  30 kg or  $\leq$  250 m, otherwise drum

Photographs are not to scale and do not represent detailed images of the respective products.

Product Management	Document: J-Y(ST)Y...LG Indoor Cable	1 / 2
--------------------	--------------------------------------	-------

U.I. Lapp GmbH	<b>DATASHEET</b>	
	<b>J-Y(ST)Y...LG Indoor Cable</b>	<b>1591502</b> <b>14.11.2013</b>

### Technical Data

Number of double cores:	3
Outer diameter (mm):	8.5
Copper index (kg/km):	31
Weight (kg/km):	80
Core identification code:	according to VDE 0815, refer to Appendix T10
Peak operating voltage:	(not for power applications) 300 V
Insulation resistance:	> 100 MOhm x km
Coupling:	(800 Hz): K1: 80% ≤ 300 pF/100m
Conductor cross-section in:	0.6 mm: 0.28 mm <sup>2</sup> 0.8 mm: 0.50 mm <sup>2</sup>
Cable attenuation/attenuation:	0.6 mm: 1.7 dB/km 0.8 mm: 1.1 dB/km
Minimum bending radius:	Fixed installation: 10 x outer diameter
Test voltage:	Core/core: 800 V Core/screen: 800 V
Loop resistance:	0.6 mm: max. 130 ohm/km 0.8 mm: max. 73.2 ohm/km
Temperature range:	Occasional flexing: -5 °C to +50 °C Fixed installation: -30 °C to +70 °C

Product Management	Document: J-Y(ST)Y...LG Indoor Cable	2 / 2
--------------------	--------------------------------------	-------