

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINDICHT® SVF-M	52107350 14.11.2013

Lateral sealing lips fit automatically around various cable dimensions
Cable-specific seal dimensions are no longer necessary
Large opening allows clamping of up to two flat cables
Optimum strain relief
Tolerance



Wide clamping range



Maximum vibration protection



Assembly time



Application range

For inserting flat cables.
Control cabinet manufacturing
Conveyor systems
Pumps
Lifts

Design

Metric connection thread acc. to EN 50262

Note

For suitable flat cables, refer to ÖLFLEX® LIFT F for indoor applications or ÖLFLEX® CRANE F for outdoor applications
Counter nut to be used: SKINDICHT® SM-M

Remark


Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article designation / size:	M 32/29
Min./max. flat cable width:	14 / 27
Min./max. cable thickness (mm):	4 / 11,5
Pieces / PU:	10
Caution:	The installation dimensions can be found in appendix T21
Material:	Body: nickel-plated brass Seal: CR
Temperature range:	-30°C to +100°C

Product Management	Document: SKINDICHT® SVF-M	1 / 2
--------------------	----------------------------	-------

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINDICHT® SVF-M	52107350 14.11.2013



Product Management	Document: SKINDICHT® SVF-M	2 / 2
--------------------	----------------------------	-------