


U.I. Lapp GmbH	<h1>DATASHEET</h1>	
	Basic Tie cable tie	61831026 14.11.2013

The Basic Tie cable tie made of PA 6.6 is the standard cable tie for many applications. It is UL recognized, resistant against several chemicals and the black cable tie is UV-resistant.



Halogen-free



UV-resistant

Info

The standard cable ties for many applications

Application range

Multipurpose cable tie for many applications

Benefits

Good UV-resistance of the black cable tie

High resistance to bases, oils, greases, oil derivatives, solvents containing chlorine

Norm references / Approvals

E-File Number: E 86244 (M)

Note

Not resistant to phenols

Limited resistance to acids

Product features

Flame retardancy: UL 94 class V2

Water absorption: 2.5 % (50 % relative humidity)

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article description:	Basic Tie 780x9.0 nat.
UL approval:	yes
Length x width (mm):	780 x 9
Bundling Ø (mm):	32 - 233
Tensile strength (N):	700
PU:	100
General:	Dielectric strength: 50,000 volts/mm For higher tensile strength
Note:	Melting point: +256 °C
Material:	Polyamide 6.6 - halogen-free
Temperature range:	-40 °C to +85 °C Max. temperature: +110 °C (short-term)

Product Management	Document: Basic Tie cable tie	1 / 1
--------------------	-------------------------------	-------