

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINDICHT® SVRN-M	52104800 14.11.2013

High mechanical stability
Optimum strain relief




Good chemical resistance



Corrosion-resistant



Mechanical resistance



Optimum strain relief



Application range

Brass cable gland with hexagonal fitting, for fast assembly with a flat spanner.

Design

Metric connection thread acc. to EN 50262

Design

For connection thread M 50 x 1.5 and M 63 x 1.5, refer to SKINDICHT® SVRE-M

Note

Counter nut to be used: SKINDICHT® SM-M

Example order identification: SVRN-M 12 / 7 / 512 = Connection thread metric7 = Function thread PG5 = Clear width F

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Product Management	Document: SKINDICHT® SVRN-M	1 / 3
--------------------	-----------------------------	-------


U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINDICHT® SVRN-M	52104800 14.11.2013

Technical Data

Article designation / size:	12 x 1,5
Function thread PG:	7
SW1/SW2 mm:	14 / 13
Overall length, C (mm):	20,6
Thread length, D (mm):	5
Clear opening F (mm):	5
Pieces / PU:	100
Caution:	The installation dimensions can be found in appendix T21
On request:	Available with long connection thread
Material:	Body: nickel-plated brass Sealing ring: CR/NBR
Protection rating:	IP 54
Temperature range:	-20°C to +100°C

Product Management	Document: SKINDICHT® SVRN-M	2 / 3
--------------------	-----------------------------	-------

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINDICHT® SVRN-M	52104800 14.11.2013



Product Management	Document: SKINDICHT® SVRN-M	3 / 3
--------------------	-----------------------------	-------