



DATA SHEET	0151003
DIN extension cable KE 1 L-SIL 2x1,5	valid from : 01.12.2008

Application

The extension cable KE 1 L-SIL 2 x 1,5 mm² are silicone insulated cores which transmit the thermoelectric voltage of Fe/CuNi thermocouples. They are for fixed installation in dry and damp rooms and may only be installed outdoors with mechanical and UV protection and in observation of the max. permitted temperature range.

Design

Conductor	1,5 mm ² (48 x 0,20 mm)
Conductor material	LX alloying, accuracy class 2 according DIN 43722 Positive conductor: Fe (iron) Negative conductor: CuNi (cupronickel)
Core insulation	Silicone compound
Core identification	Positive conductor: red Negative conductor: blue
Core layering	Cores twisted together
Outer sheath	No outer sheath

Electrical properties

Limiting deviation class 2 ± 140 µV (± 2,5 °C) / m measuring point temperature +500 °C

Mechanical and thermal properties

Temperature range	occasional flexing:	-25 °C up to +180 °C
Minimum bending radius	occasional flexing:	12 x cable diameter

Originator: Frank Hörtnagl / PD-KL Approved: Werner Körner / TE	Document: DB0151003EN	page 1 of 1
--	-----------------------	-------------