

DATA SHEET

0152023

DIN compensating cable KN 15 L-SIL-S 2x1,5 round

valid from:

01.12.2008

Application

The compensating cable KN 15 L-SIL-S 2 x 1,5 mm² is a silicone insulated cable which transmits the thermoelectric voltage of NiCr/Ni thermocouples. It is for flexible use and fixed installation in dry rooms with low mechanical load. They may only be installed outdoors with UV- and humidity protection and in observation of the max. permitted temperature range. The steel wire armouring serves as mechanical protection.

Design

Conductor 1,5 mm² (48 x 0,20 mm)

Conductor material KCA alloying, accuracy class 2 according DIN 43722

Positive conductor: Fe (iron)

Negative conductor: CuNi (cupronickel)

Core insulation Silicone compound

Core identification Positive conductor: red

Negative conductor: green

Core layering Cores twisted together

Outer sheath Silicone compound, colour: green

Galvanized steel wire braiding with interweaved green identification thread Armouring

Electrical properties

± 100 µV (± 2,5 ℃) / m easuring point temperature +900 ℃ Limiting deviation class 2

Mechanical and thermal properties

Temperature range occasional flexing: -25 ℃ up t o +180 ℃

Minimum bending radius occasional flexing: 15 x cable diameter

flame retardant in acc. to IEC 60332-1-2 resp. VDE 0482-332-1-2 **Flammability**