


U.I. Lapp GmbH	<h1>DATASHEET</h1>	
	SKINTOP® DIX-M AUTOMATION	53440980 14.11.2013

Optimal seal when using AS-I bus cables
 Easy insertion of pre-assembled cables (with fieldbus or RJ-45 connector)
 Strain relief



Automation



Assembly time



Optimum strain relief



Reliability



Temperature-resistant



UV-resistant

Application range

These seals can be used instead of our standard seals in the SKINTOP® cable glands.
 Control cabinets
 Control panels
 Office applications
 Automation technology

Design

Precise cut for AS-I bus cables
 Seal with hole and cut for easy insertion of pre-assembled RJ45 network cables
 Seal with hole and cut for easy insertion of pre-assembled field bus cables
 Multiple seal inserts with holes and slits for easy insertion of pre-assembled cables


Note

IP 68 can be achieved if the hole is optimally occupied, i.e. when using standard AS-I bus cables

Remark

Photographs are not to scale and do not represent detailed images of the respective products.


Product Management	Document: SKINTOP® DIX-M AUTOMATION	1 / 3
--------------------	-------------------------------------	-------


U.I. Lapp GmbH	<h1>DATASHEET</h1>	 LAPP GROUP
	SKINTOP® DIX-M AUTOMATION	53440980 14.11.2013

Technical Data

Article designation / size:	M 25
Number of cables x cable Ø:	1 x 5,4
Pieces / PU:	50
Colour delivered:	Black, RAL 9005
Material:	NBR
Protection rating:	IP 54
Temperature range:	-40°C to +100°C

Product Management	Document: SKINTOP® DIX-M AUTOMATION	2 / 3
--------------------	-------------------------------------	-------

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® DIX-M AUTOMATION	53440980 14.11.2013



Product Management	Document: SKINTOP® DIX-M AUTOMATION	3 / 3
--------------------	-------------------------------------	-------