

DATA SHEET

0164013

valid from : 01.12.2008

Application

The extension cable KXN 20 L 2 x 1,5 mm² is a PVC insulated cable with aluminium foil screen which transmits the thermoelectric voltage of NiCr/Ni thermocouples. It is for flexible use and fixed installation in dry and damp rooms with medium mechanical load. They may only be installed outdoors with UV protection and in observation of the max. permitted temperature range. The overlapping foil wrapping screens the cores against electromagnetical interference.

Design

Conductor	1,5 mm² (48 x 0,20 mm)		
Conductor material	KX alloying, accuracy class 2 according IEC 60584 Positive conductor: NiCr (nickelchrome) Negative conductor: Ni (nickel)		
Core insulation	PVC compound		
Core identification	Positive conductor: green Negative conductor: white		
Core layering	Cores twisted together		
Screening	aluminium cladded plastic foil with tinned copper drain wire (7x0,30 mm)		
Outer sheath	PVC compound, colour: green		
Electrical properties			
Limiting deviation class 2	\pm 100 μV (± 2,5 ${\rm C}) / m$ easuring point temperature +900 ${\rm C}$		
Mechanical and thermal properties			
Temperature range	occasional flexing:	-5 ℃ up to +70 ℃	
Minimum bending radius	occasional flexing:	15 x cable diameter	
Flammability	flame retardant in acc. to IEC 60332-1-2 resp. VDE 0482-332-1-2		

Originator: Frank Hörtnagl / PD-KL Approved: Werner Körner / TE	Document:	DB0164013EN	page 1 of 1
--	-----------	-------------	-------------