

U.I. Lapp GmbH	<h1>DATASHEET</h1>	
	EPIC® MC Module: PROFIBUS DP	10390500 14.11.2013

The mixed assembly guarantees high flexibility. For applications in mechanical and plant engineering, for printing machines and slide-in technology.

Uninterruptible fieldbus operation when pulling the connector

Transmission rate up to 12 MBit/s

Easy assembly by screw connection

Shielding connection by strain relief



Automation



Industrial machinery and plant engineering



Wind Energy



Info

Profibus DP module for uninterrupted fieldbus operation

Application range

Plant engineering

Light & sound technology

Control engineering

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data


Article:	MCS 2 BS
Version:	female
Contacts:	2 + shield
Pieces / PU:	5
Rated voltage (V):	30 V
Rated current (A):	1 A
Contacts:	Copper alloy, gold-plated
Number of contacts:	2 / 4 + shield
Termination methods:	Screw termination: for Profibus cable
Cycle of mechanical operation:	100
Temperature range:	-20 °C až +85 °C
Degree of soiling:	3

Product Management	Document: EPIC® MC Module: PROFIBUS DP	1 / 2
--------------------	--	-------


U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	EPIC® MC Module: PROFIBUS DP	10390500 14.11.2013



M



F



Product Management	Document: EPIC® MC Module: PROFIBUS DP	2 / 2
--------------------	--	-------