


U.I. Lapp GmbH	<b>DATASHEET</b>	
	<b>SKINTOP® DIX-M</b>	53350166 29.11.2013

Easy insertion of several cables into one gland  
Higher packing density allows smaller part construction



Automation



Assembly time



Optimum strain relief



Temperature-resistant



UV-resistant

### Application range

For use in SKINTOP® cable glands.

A sealing ring with several holes is used in place of the inner sealing insert.

### Design

SKINTOP® DIX-M VITON® is resistant to oil, water, alkaline solutions, acids, solvents etc.

### Note

IP 68 can be achieved when all openings are closed and all bores are optimally occupied, i.e. when using cables with nominal diameter and/or SKINTOP® DIX-DV sealing plugs

### Remark

Viton® is a registered trademark of DuPont de Nemours

Photographs are not to scale and do not represent detailed images of the respective products.

### Technical Data

Article designation / size:	50166
Size M:	M 50
Number of cables x cable Ø:	16 x 6
On request:	Special shapes
Colour delivered:	Black, RAL 9005
Material:	NBR VITON®
Protection rating:	IP 54
Temperature range:	-40°C to +100°C

Product Management	Document: SKINTOP® DIX-M	1 / 1
--------------------	--------------------------	-------