


U.I. Lapp GmbH	<h1>DATASHEET</h1>	
	Multi coaxial cables RG 59 B/U	2170056 14.11.2013

In extended systems, the use of the RG 59 B/U multi-coaxial cable as a screened supply cable prevents an accumulation of individual cables running in parallel over long distances. This saves installation costs and provides greater mechanical protection for the each sensitive cable.



Design

2 x single coaxial cables type RG 59 B/U
Twin cable
PVC sheath
Colour: black

Product features

Multi-coaxial cables provide an easier installation than individual installation

Remark

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.
Copper price basis: EUR 150/100kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.
Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths
Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Number of single cables x RG type:	2 x RG 59 B/U
Outer diameter (mm):	6,5 x 13
Copper index (kg/km):	50
Weight (kg/km):	116
Based on:	Similar to MIL specification MIL-DTL17 H
Minimum bending radius:	Fixed installation: 15 x cable diameter
Temperature range:	Fixed installation: -40°C to +80°C

Product Management	Document: Multi coaxial cables RG 59 B/U	1 / 1
--------------------	--	-------