

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® GMP-GL-M	53119170 14.11.2013

Glass fibre-reinforced for maximum mechanical stability
Supporting surface for spanner means scratches on the housing are avoided



Good chemical resistance



Assembly time



Oil-resistant



Temperature-resistant



UV-resistant



Variety of approval certifications

Application range

For locking SKINTOP® cable glands in boreholes without thread.

Design

Metric connection thread acc. to EN 50262

Norm references / Approvals

UL File Nr. E79903

Note

UL approval only when used with the UL-approved SKINTOP® polyamide cable glands
Designed for use with metric SKINTOP® plastic cable glands

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Product Management	Document: SKINTOP® GMP-GL-M	1 / 3
--------------------	-----------------------------	-------

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® GMP-GL-M	53119170 14.11.2013

Technical Data

Article designation / size:	63 x 1,5
SW (mm):	75
Pieces / PU:	25
On request:	Available without collar (without surface for assembling tool)
Colour delivered:	Silver grey (RAL 7001) Light grey (RAL 7035) Black (RAL 9005), UV-resistant
Material:	Polyamide, glass fibre-reinforced
Temperature range:	Fixed: -40°C to +100°C Dynamic: -20°C to +100°C

Product Management	Document: SKINTOP® GMP-GL-M	2 / 3
--------------------	-----------------------------	-------

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® GMP-GL-M	53119170 14.11.2013



Product Management	Document: SKINTOP® GMP-GL-M	3 / 3
--------------------	-----------------------------	-------