



ÖLFLEX® 440 P

DB 0012800

valid from: 2013-05-10

Application

ÖLFLEX® 440 P cables are cold flexible oil-resistant control cables with a core insulation of TPE and an outer sheath of Polyurethane for flexible use and fixed installation under increased mechanical load conditions. They are designed for use in dry, damp and wet conditions. Outdoor use: They may only be installed considering the temperature range.

Continuous busy movements, compulsory guidance respectively usage on cable drums or pulleys or under a strain of more than 15 N / mm² are not allowed. At room temperature they are widely resistant to certain oils and resistant to acids. The outer sheath of Polyurethane is resistant against high mechanical load, particularly to abrasion and scouring, cut resistant, microbe-proof and hydrolysis resistant. All materials used for these cables are halogen-free.

Application range: Construction machinery, machine tools, transfer lines, production plants

Design

Design	based on EN 50525-2-21 resp. VDE 0285-525-2-21 / HD 22.10 S2 resp. VDE 0282-10 EN 50525-2-51 resp. VDE 0285-525-2-51 / HD21.13 S1+A1 resp. VDE 0281-13
Approvals	up to and inclusive 2,5 mm ² : VDE Reg.-No. 6582
Conductor	fine wire strands of tinned copper acc. to IEC 60228 resp. VDE 0295, Class 5
Core insulation	Thermoplastic elastomer (TPE)
Core identification	black cores with white numbers with or without GN/YE ground conductor acc. to DIN EN 50334 resp. VDE 0293-334
Outer sheath	Polyurethane compound TMPU in acc. to EN 50363-10-2 resp. VDE 0207-363-10-2 colour: silver grey, similar 7001

Electrical properties

Nominal voltage	U ₀ / U 300 / 500 V
Test voltage	3000 V AC

Mechanical and thermal properties

Min. bending radius	occasional flexing: 12,5 x outer diameter fixed installation: 4 x outer diameter
Temperature range	occasional flexing: -40 °C up to +90 °C max. conductor temperature fixed installation: -50 °C up to +90 °C max. conductor temperature
Oil resistance	acc. to EN 50363-10-2 resp. VDE 0207-363-10-2
Halogen-free	acc. to VDE 0472-815
UV resistance	acc. to EN ISO 4892-2-2006, method A (change of colour allowed)
Flammability	flame retardant acc. to IEC 60332-1-2 resp. VDE 0482-332-1-2
MUD	MUD resistant acc. to IEC 61892-4 Annex D
Tests	acc. to IEC 60811, EN 50395, EN 50396
EC directive	This cable is conform to ECD 2006/95/EC (Low Voltage Directive) and 2011 / 65 / EU (RoHS, Restriction of the use of certain hazardous substances).