



DATA SHEET	1136752
ÖLFLEX® CLASSIC 115 CY	valid from : 16.10.2006

Application

ÖLFLEX® CLASSIC 115 CY cables are control cables for flexible use and fixed installation for medium mechanical use. They are for use in dry, damp and wet rooms. They may only be installed outdoors with UV protection and in observation of the temperature range. At room temperature it is generally resistant against acids, caustics solutions and certain oils. ÖLFLEX® CLASSIC 115 CY cables are used as supply and interconnecting cable for controlling machine tools, production lines, control equipment on conveyors, also for use in measuring regulating and computer units. Suitable for freely moved without forced guidance and tensile stress. The screen is a protection against electrical interference.

Technical data

Design	in accordance to HD 21.13S1 that is VDE 0281-13
Conductor	bare copper, fine wire strand in accordance to IEC 60 228 that is VDE 0295, class 5
Core insulation	LAPP special PVC compound P8/1, better than the PVC compound T12 in accordance to HD 21.1 that is VDE 0281 part 1
Identification	in acc. to HD 186 resp. VDE 0293, black cores with white numbers with or without green/yellow ground conductor
Wrapping Screen	insulated foil of plastic braid of tinned copper, coverage = 85 % (nominal value)
Outer sheath	PVC compound TM2 in acc. to HD 21.1 that is VDE 0281 part 1 with increased requests to LAPP specification
Nominal voltage Test voltage	300 / 500 V 4000 V AC
Temp. range	for flexible use -5 up to +70° C max. conductor temperature fixed installation -40 up to +80° C max. conductor temperature
Min. bending radius	flex. use : 20 x cable diameter fixed installation: 6 x cable diameter
Flame retardant	in acc. to IEC 60 332.1
Tests	in acc. to VDE 0472 and IEC 60 811-x.x that is VDE 0473
EC directive	This cable confirms to ECD 73/23/EEC (low voltage directive).

elaborated by: TE-K: M. Herb / O. Bautin	Document: DB1136752EN	page 1 of 1
---	-----------------------	-------------



DATA SHEET	1136752
ÖLFLEX® CLASSIC 115 CY	valid from : 16.10.2006

elaborated by: TE-K: M. Herb / O. Bautin	Document: DB1136752EN	page 2 of 1
---	-----------------------	-------------