

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® ST-HF-M	53111457 14.11.2013

SKINTOP® halogen-free
Maximum reliability
Extremely flame-retardant according to UL 94 V0
Completely halogen-free (including sealing material)
Self-extinguishing, no dripping
Permanent vibration protection



Good chemical resistance



Wide clamping range



Halogen-free



Variety of approval certifications

Info

Cable gland for railway applications- Fire protection on railway vehicles Approval according to DIN EN 45545-2:2013

Application range

When the protection of people and property is a priority.

Public buildings

Ventilation systems

Tunnel construction

Underground railways and trains

Design

Metric connection thread acc. to EN 50262

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Product Management	Document: SKINTOP® ST-HF-M	1 / 3
--------------------	----------------------------	-------


U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® ST-HF-M	53111457 14.11.2013

Technical Data

Article designation / size:	ST-HF-M 40 x 1,5
Clamping range ØF (mm):	19-28
SW (mm):	46
Overall length, C (mm):	52
Thread length, D (mm):	10
Pieces / PU:	10
Caution:	Refer to Appendix T21 for the installation dimensions and torques
Colour delivered:	Light grey (RAL 7035)
Material:	Polyamide UL 94V-0 - halogen-free Sealing ring: LSE 1 - halogen-free O-ring: LSE 1 - halogen-free
Tests:	Filament wire test EN 60695-2-1/1 +960°C
Protection rating:	IP 68 - 5 bar
Temperature range:	-20°C to +100°C

Product Management	Document: SKINTOP® ST-HF-M	2 / 3
--------------------	----------------------------	-------

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® ST-HF-M	53111457 14.11.2013



Product Management	Document: SKINTOP® ST-HF-M	3 / 3
--------------------	----------------------------	-------