


U.I. Lapp GmbH	DATASHEET	
	EPIC® STA 14 Solder termination	10492200 14.11.2013

The proven STA inserts for screw termination and solder termination.
 STA inserts - proven by the strong contact springs.
 The proven STA inserts for screw termination and solder termination.



Industrial machinery and plant engineering



Application range

Control systems
 Rack technology
 Electronic laboratory

Remark


Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article:	STA 14 FL
Version:	female
Contacts:	1 - 14
Pieces / PU:	5
Rated voltage (V):	IEC: 24 B AC, 60 B DC UL: 48 B CSA: 48 B
Rated current (A):	IEC: 7.5 A UL: 7.5 A CSA: 7.5 A
Contact resistance:	< 3 mOhm
Contacts:	Copper alloy, tinned
Number of contacts:	14
Termination methods:	Solder termination: up to 1.5 mm ²
Cycle of mechanical operation:	100
Temperature range:	-40°C až +80°C
Degree of soiling:	2




Product Management	Document: EPIC® STA 14 Solder termination	1 / 2
--------------------	---	-------

U.I. Lapp GmbH	<h1>DATASHEET</h1>	
	EPIC® STA 14 Solder termination	10492200 14.11.2013



M

F



Product Management	Document: EPIC® STA 14 Solder termination	2 / 2
--------------------	---	-------