U.I.	Lapp
Gn	nbH

# DATASHEET



## UNITRONIC® BUS ASI FD

2170358 14.11.2013

### Highly flexible application

The new BUS ASI LD 2 x 2.5 (Long Distance) allows even modules located further away to be connected. AS-I power supplies can be reduced. The BUS ASI LD is downwards-compatible with version 1.5. For highly flexible applications (power chains, moving machine parts) High oil-resistance

## LAPP KABEL STUTTGART UNITRONIC® BUS ASI FD

# LAPP KABEL STUTIGART UNITRONIC® BUS ASI FD





Automation



Halogen-free



Industrial machinery and plant engineering



Power chain



Temperature-resistant

Info "FD" = suitable for power chains "LD" = Long Distance

#### Application range

Communication at sensor/actuator level UNITRONIC® Fieldbussensor-/actuator wiring

#### Design

Extra-fine wire, tinned copper strands Core insulation: blue and brown Profiled outer sheath: TPE or PUR Colour: yellow (RAL 1023) or black (RAL 9005)

#### Norm references / Approvals

ASI is standardised Europe-wide in EN 50295 and internationally in IEC 62026-2. TPE variant: UL AWM Style 2103CSA AWM II A/B PUR versions: UL AWM Style 20549

Product Management	Document: UNITRONIC® BUS ASI FD	1 / 3

# DATASHEET



## UNITRONIC® BUS ASI FD

2170358 14.11.2013

### Product features

PUR versions are halogen-free according to IEC 60754-1

Flame-retardant according to IEC 60332-1-2, UL FT-2 flame test

Data and power are transmitted via an unscreened, geometrically coded two-core flat cable (protection against polarity reversal).

The conductor is contacted by "piercing technology" within the ASI modules.

The sensors are connected to the ASI modules (coupling modules) using round cables (connection cables).

#### Remark

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths Lapp Kabel is a member of the AS-International Association

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data Article designation:	UNITRONIC® BUS ASI FD P FRNC
-	
Outer sheath material:	PUR UL/CSA (AWM)
Outer sheath colour:	black
Application:	Transmission of 30 V DC auxiliary power
Number of cores and mm <sup>2</sup> per conductor:	2 x 1,5
Copper index (kg/km):	29
Weight (kg/km):	64
Peak operating voltage:	300 V (not for power applications)
Conductor resistance:	1.5 mm²: max. 13.7 Ohm/km 2.5 mm²: max. 8.21 Ohm/km
Minimum bending radius:	Fixed installation: 12 mm Flexing without fixing: 24 mm Flexing with fixing: 60 mm (15 x D)
Test voltage:	Core/core: 2000 V
Temperature range:	Fixed installation: -40°C to +80°C (TPE +105°C) Flexing – without fixing: -30 °C to +70 °C (TPE +105 °C)

Product Management	Document: UNITRONIC® BUS ASI FD	2/3
PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved Photographs are not to scale and do not represent detailed images of the respective products.		

# DATASHEET



# UNITRONIC® BUS ASI FD

2170358 14.11.2013

 Product Management
 Document: UNITRONIC® BUS ASI FD
 3 / 3

 N 0486 / 01 03.10
 ©2012 Lapp Group - Technical changes reserved