



Data Sheet	2170340
UNITRONIC® DeviceNet™ THICK halogen free UL/CSA (CMG)	Valid from: 26.10.2006



Design

a) Pair 02YS(ST) 1X2X1.3/3.8-120

Wire

Stranded tinned copper wire 19 X 0.25

∅ 1.3 mm (0.051 in)

Insulation of foamed Polyethylene (PE) with skin, halogen free

∅ 3.8 mm (0.150 in)

Wall thickness approx. 1.2 mm

2 wires, white (WH) and blue (BU) side by side

Alulaminated foil overlapped, applied longitudinally

b) Pair LI2Y(ST) 1X2X1.5/2.7

Wire

Stranded tinned copper wire 19 X 0.34

∅ 1.7 mm (0.067 in)

Insulation of Polyethylene (PE), halogen free

∅ 2.7 mm (0.106 in)

Wall thickness approx. 0.5 mm

2 wires, red (RD) and black (BK) side by side

Alulaminated foil overlapped, applied longitudinally

Core

Central element: Stranded tinned copper drain wire 0.86 mm² (19x0.24)

1 Pair 02YS(ST) 1X2X1.3/3.8-120 LI VZN

1 Pair LI2Y(ST) 1X2X1.5/2.7 VZN

+ fillers

Shield braiding of tinned copper wires 0.13 mm diameter,
coverage approx. 70%

∅ 8.6 mm (0.339 in)

Jacket

Thermoplastic copolymer (FRNC) violet (VT), halogen free

Wall thickness approx. 1.8 mm

∅ 12.2 ±0.3 mm (0.480 ±0.012 in)

Marking: LAPP KABEL STUTTGART UNITRONIC® DeviceNet™ THICK halogen free UL/CSA

1x2xAWG18 + 1x2xAWG15 (SHIELDED) * (UL) E224252 CMG 75°C or PLTC FT4

Sun Res * ROHS ART. 2170340

prepared by: PD-KL: Hans Euler	Document: DB2170340EN	Page 1 of 2
-----------------------------------	-----------------------	-------------



Data Sheet	2170340
UNITRONIC® DeviceNet™ THICK halogen free UL/CSA (CMG)	Valid from: 26.10.2006

Electrical data at 20°C

Conductor resistance (data, AWG18)	(Pair a)	≤	22.6	Ohm/km
Conductor resistance (power, AWG15)	(Pair b)	≤	11.7	Ohm/km
Capacitance (1 kHz core/core)	(Pair to a)	≈	39.8	nF/km
Characteristic impedance (1 MHz)	(Pair to a)		(120 ±12)	Ohm
Signal run time	(Pair to a)	≤	4.46	ns/m
Capacity unbalanced to ground	(Pair to a)	≤	3937	pF/km
Operating voltage		=	24	V
Operating voltage (peak)		≤	300	V
Insulation resistance		≥	200	MOhm*km
Test voltage (core/core/screen rms 50 Hz 1min)		=	2000	V

Frequency (kHz)	125	500	1000
Attenuation typ. (dB/100m) (Pair to a) (dB/100ft)	0.42 (0,1)	0.81 (0,2)	1.31 (0.4)

Mechanical and thermal characteristics

Conductor/Screen material acc. to DIN EN 13602 Cu-ETP-A...-B
 Insulation material acc. to DIN EN 50290-2-23 (VDE 0819), table 2/A (HD 624.3)
 Insulation material acc. to DIN EN 50290-2-23 (VDE 0819), table L/MD (HD 624.3)
 Jacket material acc. to DIN EN 50290-2-27 (HD 624.7)
 Sunlight resistant acc. to UL 1581 Sec.1200
 Flame retardant acc. to UL 1685 (CSA FT 4)

Application / Special feature:

NEC Class 2

Permissible temperature range : -25°C (-13°F) up to +80°C (+176°F)

min. bending diameter allowed : multiple 20 X ø
 single 7.5 X ø

Weight approx. : 195 kg/km (130.7 lb/1000ft)