

DATA SHEET	52032580
SKINDICHT® CN-M	valid from : 07.02.2008

The SKINDICHT® CN-M is an chromium nickel steel cable gland with metric connecting thread with VITON® seal, specially designed for use under tough conditions, e.g. in the pharmaceutical, petrochemical industry (aggressive media) as well as offshore-, dairy- and food area. Suitable counter nut SKINDICHT® SM M CrNi.



Components:

Dome nut:	Chrome-nickel-steel, material no. 1.4305 (V2A)
Body:	Chrome-nickel-steel, material no. 1.4305 (V2A)
Seal:	FPM
O-Ring:	FPM

Technical feature:

Connecting thread:	M 12 x 1.5 up to M 63 x 1.5 in acc.to DIN 60 423 Tab.1
Clamping range:	3.5 mm up to 52.0 mm
Temperature range:	-25°C up to +200°C
Protection class:	IP 68
Tensile strength:	in acc.to EN 50262, Type A

For more information please see our current catalogue.
Please do not hesitate to contact our laboratory if there any questions regarding resistance against aggressive agents and special oil.