

DATA SHEET

UNITRONIC® BUS LD UL/CSA ... x 2 x 0,22 mm²

gültig ab :

27.10.2009

2170803

Application

UNITRONIC® BUS LD UL/CSA is a screened, twisted paired cable for bus systems with a data transmission rate up to 10 MBit/s. The twisting of the conductors into pairs ensures maximum interference suppression of the individual signals. The copper screening protects against external electromagnetic influences. Cables of this composition are intended for limited flexible use and for permanent installation in dry and damp interiors.

Approval: UL/CSA Type CMX acc. to UL 444 and CSA C22.2 No. 214-02

Applicable connectors: D-Sub-Connector, 9-pins; Round-Connector, 9-pins (system of protection IP 65)

Design

Conductor multiple wire stranding of bare copper wires

Insulation special PE-based compound

Core identification acc. to DIN 47100

Stranding Cores twisted into pair, pairs twisted together

Wrapping plastic foil

Screening braiding of tinned copper wires
Sheath special PVC-based compound
Sheath colour violet similar to RAL 4001

CableØ 1 pair approx. 5,7 mm (part no. 2170803)
CableØ 2 pairs approx. 7,1 mm (part no. 2170804)
CableØ 3 pairs approx. 7,2 mm (part no. 2170805)

Electrical properties at 20 ℃

Conductor resistance (loop)	max. Ω/km	186
Insulation resistance	min. $G\Omega$ x km	5
Mutual capacitance at 800 Hz	max. nF/km	60
Characteristic impedance	Ω	100 - 120
Attenuation at 100 kHz	nom. dB/100m	0,9
Attenuation at 1 MHz	nom. dB/100m	2,5
Near-end cross talk attenuation at 1 MHz	min. dB	50
Near-end cross talk attenuation at 10 MHz	min. dB	40
Transfer impedance at 30 MHz	max. m Ω /m	250
Nominal velocity of propagation	nom.	0,66 c
Signal transit time	nom. ns/m	5,06
Operating voltage (not for power purposes)	peak value V	250
Test voltage (conductor/conductor)	V	1500
Test voltage (conductor/screen)	V	1000

Mechanical and thermal properties

Permissible temperature range (fixed use)	$^{\circ}$	-40 to +80
Permissible temperature range (flexible use)	$^{\circ}$	-5 to +70
Minimum bending radius (fixed use)	cableØ x	8
Minimum bending radius (flexible use)	cableØ x	20
Flame propagation	flame retardant to IEC 60 332-1-2	

Conformity

This cable confirms to RoHS directive (2002/95/EG)

elaborated by: Petra Samek, PDC	Dokument:	DB2170803EN04	page 1 of 1
------------------------------------	-----------	---------------	-------------

Nr.: 0019/0408