

U.I. Lapp GmbH	DATASHEET	
	SKINDICHT® FL	52008040 14.11.2013

The seal profiles enable many problems to be solved
Several flat and round cables can be fed through at the same time
Through the internal conical contour in the upper part of the housing, the sealing inserts are pressed onto the cable



Robust

Application range

Cable flange that can be used universally, mainly for large flat cables.

Lifts

Conveyor systems

Crane and conveying machinery

Power chains

Note

When assembled professionally and properly, the protection class of IP 65 can be reached


For suitable flat cables, refer to ÖLFLEX® LIFT F for indoor applications or ÖLFLEX® CRANE F for outdoor applications

Remark

Photographs are not to scale and do not represent detailed images of the respective products.



Technical Data

Article designation / size:	FL 4
Cable pass length x width in mm:	63 x 12,0 (+0,2)
Dimensions: L x W x H (mm):	45 x 35 x 95
Pieces / PU:	1
Material:	Body: aluminium, special untreated alloy Screws and spring washers: zinc-plated steel Seal: NBR
Protection rating:	IP 65
Temperature range:	-20°C to +100°C



Product Management	Document: SKINDICHT® FL	1 / 2
--------------------	-------------------------	-------

U.I. Lapp GmbH	<h1>DATASHEET</h1>	 LAPP GROUP
SKINDICHT® FL		52008040 14.11.2013



Product Management	Document: SKINDICHT® FL	2 / 2
--------------------	-------------------------	-------