

|                   |                        |                                                                                                      |
|-------------------|------------------------|------------------------------------------------------------------------------------------------------|
| U.I. Lapp<br>GmbH | <b>DATASHEET</b>       |  <b>LAPP GROUP</b> |
|                   | <b>SKINDICHT® MR-M</b> | <b>52104320</b><br><b>14.11.2013</b>                                                                 |

Enables the use of cable glands with smaller connection threads than the existing threaded holes



Space requirement



Reliability



Connector with standard housing unit

### Application range

Machines  
Devices  
Housings

### Design

Metric connection thread acc. to EN 50262

### Remark

Photographs are not to scale and do not represent detailed images of the respective products.

### Technical Data

|                    |                                          |
|--------------------|------------------------------------------|
| Thread, male M1:   | 50 x 1.5                                 |
| Thread, female M2: | 40 x 1.5                                 |
| Pieces / PU:       | 10                                       |
| On request:        | Also available with pre-installed O-ring |
| Material:          | Nickel-plated brass                      |
| Temperature range: | -60°C to +200°C                          |

|                    |                           |       |
|--------------------|---------------------------|-------|
| Product Management | Document: SKINDICHT® MR-M | 1 / 1 |
|--------------------|---------------------------|-------|